

19999 Counts True-RMS AC/DC Voltage Current Voltmeter Capacitance Digital Multimeter

SPECIFICATION

XEAST®

Brand Name: XEAST

Model Number: XE-219

Color: Red & Black

Operating Temperature: 0 - 40 °C

Operating Humidity: <75%RH

Storage Condition: -20~60°C

Storage Humidity: < 80%

Operating Mode: Auto/Manual Ranging

Display: 19999 Counts

Material: ABS

Update Rate: 3 times per second

True RMS: yes

Data Hold: yes

Backlight: yes

Low Battery indication: yes

Auto Power Off: yes

Measuring Capacitance Range:

9.99nF/99.99nF/999.9nF/9.99μF/99.99μF/999.9μF/9.999mF

Frequency: 99.99Hz/999.9Hz/9.999KHz/99.99KHz/999.9KHz/9.999MHz

DC Voltage: 1.9999V/19.999V/199.99V/1000V/19.999mV/199.99mV

AC Voltage: 1.9999V/19.999V/199.99V/750V/19.999mV/199.99mV

DC Current:1.9999A/19.999A/19.999mA/199.99mA/199.99μA/1999.9μA

AC Current: 1.9999A/19.999A/19.999mA/199.99mA/199.99μA/1999.9μA

Resistance: 199.99Ω/1.9999Ω/19.999kΩ/199.99 kΩ/1.9999MΩ/19.999MΩ
/199.99 MΩ

Capacitance: 9.999nF/99.99nF/999.9nF/9.999μF/99.99μF/999.9μF/9.999mF

Measuring Temperature Range: -20~1000°C /-4°F-1832°F

Duty Cycle: 1%-99%

Diode Test: yes

Continuity Test: yes

NVC: yes

Power Supply: 2 * 1.5V AA Battery (not included)

Item dimension:

Item Size: 18cm * 9cm*4.5cm/7.1 * 3.5 * 1.8in

Item Weight: 356g/12.6oz

PRODUCT PICTURES

XEAST®





90mm

180mm

45mm

19999 Backlight LCD Display

19999 high precision counts digital backlight LCD monitor offers large test capacity as well as clear reading.



Anti-dropping

It is well protective by PVC anti-dropping cover and anti-fracture bracket.

1.



2.



3.



True RMS

The RMS/DC transform avoids the influence of voltage/ current waveform distortion on can even test high accuracy.





● PACKAGE INCLUDE

XEAST®

- 1 x Digital Multimeter**
- 1 x Pair of Test Leads**
- 1 x Temperature Sensor Probe**

● TERMS OF TRADE

XEAST®

1). Terms of Payment:

We accept [T/T](#), [L/C](#), [Paypal](#), [MoneyGram](#) and [Western Union](#).
30% deposit and other 70% balance before shipment.

2). Terms of Shipping:

It depends on clients order quantity and your special request. We often adopt Express ([DHL](#), [TNT](#), [UPS](#), [FEDEX](#), [EMS](#), [SPSR](#), [139 express](#) and so on), [LCL](#), [FCL](#).

Items will be careful checking before shipment, and we will update the delivery status timely after the good

s are sent out.

COMPANY INFORMATIONS

XEAST®

